




P25 PICO-HOOK ADAPTOR with .025" (.635mm) SQUARE PIN




Part Number	Description
P25-(color)	Pico-Hook with 025" Square Pin, Gold Plated
P25-S	Assortment - 1 each of 10 Solid Colors
P25-14S	14 Hook Kilo-Color Assortment
P25-16S	16 Hook Kilo-Color Assortment
P25SS-(color)	Pico-Hook with 025" Square Pin, Stainless Steel
P25SS-S	Assortment - 1 each of 10 Solid Colors

Colors: Black, Brown, Red, Orange, Yellow, Green, Blue, Violet, Gray and White PLUS Kilo-Color Capability See inside back cover for Kilo-Color Ordering Information.


Construction: P25 Is A One-Piece, Gold-Plated Beryllium Copper Blade That forms Hook, Conductor, and .025" Square Pin. P25SS Is One Piece Stainless Steel Contact Blade. Both P25 and P25SS permit connection to .025" Square or .030" Round Push-On Jumpers. Hook is designed for connection directly to a single leg of a DIP or to other components with a maximum diameter of .025". Lightweight and Finger-eze Hypo Action permit hook ups to delicate wires where weight and leverage may damage component. Barrier on tip prevents shorting between DIP legs.



E-Z-PICO-HOOK™ TEST LEADS




The E-Z PICO-HOOK is designed specifically for narrow test contact access. Illustrated by integrated circuit in-line pins. An ultra-thin blade and housing allows connector stacking and easier access.




EXTENDED HOOK DETAIL

SCALE 4X FULL SIZE
ALL DIMENSIONS ARE IN INCHES



Actual Size

Patent Applied for



COLOR CHART	
Black	Green
Brown	Blue
Red	Violet
Orange	Grey
Yellow	White

PICO-HOOK: One-Piece, Gold Plated Conductor and Hook per MIL G45204. Made for connections over component leads up to .025" (.635mm) diameter. Durable plastic body and plunger. Stainless steel compression spring provides approximately 8 ounces (227 grams) contact pressure.

LEAD WIRE: 28AWG 19 x 40 T.C. PVC insulation.
24AWG 19 x 36 S.C. Teflon insulation to 200°C.

- COLOR CHOICES**
1. Single Color Unit: Add desired color to Part No. See Color Chart.
 2. Color Assortment (1 each of 10 Colors): Add -S after Part Number.
 3. Multicolor Unit: See Kilo-Color Ordering Information on inside back cover.

For Non-Magnetic Pico-Hook add -NM to part number Example: P713-NM-(Length)